



ENGLISH

## Datasheet

# 25m Long Blue Rubber Hose, Applications Oxygen, 6.3mm Inner Diam.

RS Stock number 486-473

Type : Welding Hose

Type No. : 2802

Application : Oxygen

Standard Length : 50

Description :

Lightweight, flexible, smooth, blue hose for oxygen, to EN559. For use with industrial autogenic welding equipment, usually together with red acetylene hose. Also ideal for natural gas and air. Please contact Codan for further information.

Working Temperature : -25°C to +80°C

Std. Branding : CODAN 2802 - EN 559 - 2 Mpa (20 bar) - dim - year - sn.

Reinforcement : PVA

Inside : SBR

Colour : Black

Outside : EPDM

Colour : Blue

Standards : EN 559: 2003

### Data

Inside dia. mm	Outside dia. mm	Working Pressure BAR	Burst Pressure BAR	Bend Radius mm	Weight g/m	Product number
6.3	13.3	20	60	63	146	2802006
8.0	14.6	20	60	80	172	2802008
10.0	17.0	20	60	100	203	2802010
12.5	19.4	20	60	125	257	2802013
20.0	27.2	20	60	200	399	2802019

### Illustration

