



ENGLISH

Datasheet

## RS Pro 25m Long Orange Rubber Hose, Applications Butane, Liquefied Petroleum Gas, Propane, 6.3mm Inner Diam.

RS Stock No: **486-570**



### Product Details

RS Pro rubber hose in orange colour, measures 25 m and has an inner diameter of 6.3 mm throughout the length. This flexible hose is perfect for carrying liquefied petroleum gas (LPG), propane and butane. This hose is primarily suitable for use in industrial welding and cutting applications.

### Features and Benefits

- Ester reinforcement
- Suitable for LPG (propane and butane varieties for example)
- Orange outside and black inside
- Not antistatic
- Meets requirements of EN 559:2003

**Specifications:**

Colour	Orange
Inner Material	NBR
Outer Material	EPDM
Suitable Applications	Butane, Liquefied Petroleum Gas, Propane
Inner Diameter	6.3 mm
Length	25 m
Bend Radius	40 mm
Burst Pressure	60 bar
Outside Diameter	13.3 mm
Standards Met	EN 559: 2003
Working Pressure	20 bar
Operating Temperature Range	-30 to +80°C