



ENGLISH

Datasheet

25m Long Orange Rubber Hose, Applications Butane, Liquefied Petroleum Gas, Propane, 10mm Inner Diam.

RS Stock number 486-586



Reinforcement : Ester

Inside : NBR Colour : Black
Outside : EPDM Colour : Orange
Standards : EN 559: 2003

Data

| Inside dia. mm | Outside dia. mm | Working Pressure BAR | Burst Pressure BAR | Bend Radius mm | Weight g/m |
|-------------------|--------------------|-------------------------|-----------------------|-------------------|---------------|
| 5.0 | 11.4 | 20 | 60 | 40 | 116 |
| 6.3 | 13.3 | 20 | 60 | 40 | 141 |
| 8.0 | 15.0 | 20 | 60 | 40 | 173 |
| 10.0 | 17.0 | 20 | 60 | 50 | 203 |
| 11.0 | 18.0 | 20 | 60 | 55 | 221 |