

Professionally approved products. Datasheet

Female Solder D-Sub Connector Power Contact

RS Stock number 251-526



Specifications:

-Current at AMB. 5.5 A at 20° / 4 A at 70°

−Contact resistance ≤15m Ω according to DIN 41640 Teil 4 test 2a −Insulation resistance ≥10 M Ω according to DIN 41640 teil 7 test 3a

TEST VOLTAGE according to DIN 41640 teil 21

contact/contact 1550V eff
contact/ground 2500V eff

-Insertion force ≤75N

-Mechanical endurance -class 1 500 matings unmatings according to DIN41640 teil 21

-class 2 400 matings unmatings according to DIN41640 teil 21

-Material insulator Polyester UL94V0
-Material contacts Copper alloy

-Finishing contact surface Gold over nickel Lead Free

-Finishing termination Lead-Free

-Schock ≤30mΩ according to DIN 41640 Teil 14 test 6c -Vibration -class 1 10-2000Hz/20g according to DIN 41640 Teil 15

-class 2 10-500Hz/5g according to DIN 41640 Teil 15



Professionally approved products. **Datasheet**

