

Datasheet

RS Pro 3168 Piece Stainless Steel Screw/Bolt Kit, M2, M2.5, M3, M4, M5, M6

RS Stock No: **281-978**



Product Details

RS Pro screw/bolt kit contains 3168-pieces of M2, M2.5, M3, M4, M5 and M6 threaded screws. The screw/bolt with slot drive, is made of A2 grade 18/8 stainless steel.

Features and Benefits


- Flat, pan head
- Machine screw
- Sold as pack of 3168

Specifications:

Drive Type	Slot
Finish	Plain
Head Shape	Flat, Pan
Material	Stainless Steel
Number of Pieces	3168
Screw/Bolt Length Longest	25 mm
Screw/Bolt Length Shortest	6 mm
Screw/Bolt Type	Machine Screw
Screw/Bolts Lengths	6 to 25 mm
Stainless Steel Type	304, A2
Thread Size	M2, M2.5, M3, M4, M5, M6
Specification	DIN 85, DIN 963A, DIN 934, DIN 125



281-978



- GB** Machine screw kit ISO metric slotted stainless steel
- D** ISO-metrisches Schlitzkopf-Maschinenschrauben-Sortiment, rostfreier Stahl
- F** Kit de vis à métaux fendues, en acier inoxydable, filetage métrique ISO
- I** Corredo di viti a macchina metriche ISO intagliate in acciaio inossidabile
- E** Juego de tornillos para metales, ISO, de rosca métrica, cabeza ranurada, acero inoxidable

M5 X12 20X M5 X16 12X M5 X 25 12X	M4 X10 50X M4 X16 20X M4 X25 15X	M3 X10 40X M3 X12 30X	M3 X6 40X M3 X20 30X	M2.5 X6 90X M2.5 X12 90X	M2 X6 100X M2 X12 100X
M6 X12 10X M6 X20 10X M6 X25 10X	M5 X12 20X M5 X20 10X M5 X25 15X	M4 X12 40X M4 X16 30X M4 X20 20X	M3 X6 60X M3 X12 80X M3 X20 40X	M6 X25 10X	M6 X12 15X M6 X16 10X
M6 65X M6 65X	M5 89X M5 89X	M4 175X M4 175X	M3 385X M3 385X	M2.5 140X M2.5 140X	M2 200X M2 200X