

Datasheet

RS Pro M20 White Nylon Cable Gland, 7 to 10mm Cable Dia Range, IP66

RS Stock No: **361-1372**



Product Details

RS Pro nylon cable gland in white colour, has a thread size of M20. It has a cable diameter ranging from 7 to 10 mm. The cable made of plastic is IP66 rated. This gland is designed for the fire alarm installers to anchor the MI seal assembly into any enclosure. It is specifically used when a clean earth system or separate earth circuit is required and also when terminating MI cables into plain hole accessory boxes. It is frequently found that the gland and seal protrude into the box preventing fitting of the accessory. The insulated gland overcomes this problem. It has the advantage of being one gland size to accommodate 8 sizes of cable.

Features and Benefits

- Made of nylon 66
- IP66 rated
- Operating temperature range of -10 to +90°C



Specifications:

Cable Diameter Range	7 to 10 mm
Colour	White
IP Rating	IP66
Material	Nylon 66
Maximum Cable Diameter	10 mm
Maximum Operating Temperature	+90°C
Minimum Cable Diameter	7 mm
Minimum Operating Temperature	-10°C
Operating Temperature Range	-10 to +90°C
Thread Size	M20