



Datasheet

6 Gang Distribution Unit

RS Stock number: 374-143



Description:

BS1363 Surge & RFI protected range is an ideal solution for home, office and industrial use. The ruggedized ABS plastic or Aluminium cases ensure a high impact resistance and long working life. Unit is supplied with a detachable IEC lead for ease of cable routing unless otherwise requested. The internal surge suppressors are tested against 'worst case' conditions, as defined in International Standards IEEE C62.41-1991 Cat B3 and comply with the recommendations of BS6651:1999 Annex C.

Specification:

Voltage Rating (Nominal): 230V rms Maximum Current Rating: 10A Power Consumption: Negligible

Lead Length: 2m

Surge Handling (8/20us) [Per Element]: 19.5kA [6.5kA] Average Attenuation, Symmetric 1-30MHz (dB): -50 Voltage Protection Level (Up) 8/20us: 900V@3kA 8/20us

Response Time: <10ns

BS6651:1999 Annex C Location Category: A & B

Standard Features:

- Red status indicator to show mains power/fuse OK.
- IEC C14 Inlet connector on unit & detachable 2m lead.

Options:

- 2, 4, 6 or 8 way.
- Choice of Fire retardant ABS or Aluminium case.
- Choice of standard BS 1363 or RCD plug.
- Various additional Features.

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.