



ENGLISH

Datasheet

RS Pro Black Neoprene Rubber Sheets, 1000mm x 1200mm x 6mm

RS Stock No: **506-3191**



Product Details

RS Pro neoprene rubber sheet in black colour, is suitable for use in outdoor applications, where resistance to atmospheric ageing sunlight and seawater are required. This neoprene rubber sheet measures 1000 x 1200 x 6 mm and comes with great hardness and density.

Features and Benefits

- Can be used in outdoor applications where resistance to atmospheric ageing sunlight and seawater are required
- Hardness IRHD 60°
- Density 1.4 g/cm³

**Specifications:**

Colour	Black
Suitability	Animal Oil, Cold Water, Dilute Acid, Dilute Alkali, Ethylene Glycol, Fuel, Hot Water, Vegetable Oil
Density	1.35 g/cm ³
Length	1000 mm
Maximum Operating Temperature	+70°C
Minimum Operating Temperature	-10°C
Thickness	6 mm
Width	1200 mm
Hardness	60±7 Shore A
Material	Neoprene Rubber
Tensile Strength	5 N/mm ²