

Datasheet

RS Pro 0.12 to 1.5 L/min Flow Controller, M12 Connector, Pulse, 4.5 to 24 V dc

RS Stock No: **511-3959**



Product Details

RS Pro flow controller has a maximum pulse rate of 0.12 to 1.5 L/min. It takes 4.5 to 24 V dc supply voltage to produce a pulse control output. It offers excellent performance for a wide range of process fluids. It includes M12 connector for electrical connections.

Features and Benefits

- Suitable for a wide range of process fluids
- Excellent performance
- Traceable calibration certificate



ENGLISH

Specifications:

Control Output	Pulse
Current Rating	10 mA
Display Screen	No
Electrical Connection	M12 Connector
Maximum Flow Rate	0.12 to 1.5 L/min
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-25°C
Pipe Diameter Range	1/4 in
Supply Voltage	4.5 to 24 V dc