

Datasheet

RS Pro 5000mm PVC Reinforced Aluminium Foil HVAC Ducting, 200mm diameter

RS Stock No: **679-8712**



Product Details

RS Pro HVAC ducting measures 200 x 5000 mm and has PVC reinforced aluminium foil construction. It has a covered, metal, corrosion-resistant spiral helix, which allows the ducting to be compressed and provides good crush and kink resistance during handling and installation. This ducting is suitable for operating temperatures ranging from -5 to +90°C.

Features and Benefits

- Both types have a covered, metal, corrosion-resistant spiral helix, which allows the ducting to be compressed
- Offers good crush and kink resistance during handling and installation
- Fire retardant to meet the requirements of BS476: parts 6, 7 and 20
- Operating temperature of -5 to +90°C



Specifications:

| | |
|-------------------------------|-------------------------------|
| Diameter | 200 mm |
| Length | 5000 mm |
| Material Type | PVC Reinforced Aluminium Foil |
| Maximum Operating Temperature | +90°C |
| Minimum Operating Temperature | -5°C |
| Operating Temperature Range | -5 to +90°C |