

RS Part Number: **7737989**
 Europa Part Number: **LBDI636P**
 Specifications and dimensions



- Rotary Isolator For Din Rail Mount
- Complete With Shaft and Handle
- Din Rail Mount Switch

Dimensions:	
Height	87mm
Width	139mm
Depth	56mm
Handle:	
Height	64mm
Width	139mm
Depth	42mm
Shaft:	
Length	282mm
Weight	0.677Kg
Features	
Rated operational voltage Ue IEC &EN	690V
Rated operational voltage Ue UL	600V
Rated impulse withstand voltage Uimp	6kV
Rated uninterrupted current Iu	63A
Rated operational current Ie AC22A	63A
Rated operational current Ie AC21A	80A
Rated operational current Ie AC1	80A
Rated operational power AC23A (50/60Hz) 230V	30kW
Rated operational power AC23A (50/60Hz) 415V	37kW
Rated operational power AC23A (50/60Hz) 690V	45kW
Rated operational power AC3 (50/60Hz) 230V	22kW
Rated operational power AC3 (50/60Hz) 415V	22kW
Rated operational power AC3 (50/60Hz) 690V	30kW
UL power rating 3 phase DOL 110V	7.5hp
UL power rating 3 phase DOL 230V	15hp
UL power rating 3 phase DOL 480V	25hp
UL power rating 3 phase DOL 600V	30hp
UL power rating 1 phase DOL 110V	3hp
UL power rating 1 phase DOL 230V	7.5hp
UL short circuit fuse rating class J	70A
UL rated fused short circuit current	10kA
IEC short circuit capacity max fuse size GI	63A
IEC rated fused short circuit current	30kA
Maximum terminal capacity	25mm ²
Recommended tightening torque	2Nm
Related Products	
Neutral contact early make/late break	LB263AUXEM
Volt free contact 1NC + 1NO	LBAC16RM
Volt free contact 2NO	LBAC16RM2NO
Main pole contact	LB263MAINPOLE
Extended Main Pole + 1NC/1NO Auxiliary	LB263ERMC
Extended Neutral + 1NC/1NO Auxiliary	LB263ERNC
Gasket to provide IP65 rating	LBGASKET