

Datasheet

RS Pro 5.5 kW Automatic 3P DOL Starter, 230 V ac, 3 Phase, IP65

RS Stock No: **725-5503**



Product Details

RS Pro 5.5 kW automatic 3-phase DOL starter measures 193 x 88 x 134 mm. This enclosed, direct-on-line motor starter combines high performance and low cost. It includes options with and without isolator and support for motors from 5.5 kW to 11 kW. The options without isolator have space to mount additional 17.5 mm wide module such as a timer, level control or monitoring relay. The moulded plastic case provides IP65 ingress protection.

Features and Benefits

- Operating temperature range: -25 to +60°C
- Range available with and without isolator
- Voltage rating of 230 V ac
- 3 poles
- DOL starter
- Compliant with standards IEC/EN 60947-1 and IEC/EN 60947-4-1

Specifications:

Additional Features	Disconnect Switch Not Included
Enclosure	Yes
Motor Starter Functionality	Automatic
Motor Starter Type	DOL
Phase	3
Standards Met	RoHS Compliant; IEC/EN 60947-1; IEC/EN 60947-4-1
Overall Depth	134 mm
Overall Length	193 mm
Overall Width	88 mm
Current Rating	9 to 14 A
IP Rating	IP65
Number of Poles	3
Power Rating	5.5 kW
Voltage Rating	230 V ac
Motor Supporting Range	5.5 to 11 kW
Operating Temperature	-25 to +60°C