

ENGLISH

Datasheet

RS Pro 11 kW Automatic 3P DOL Starter, 230 V ac, 3 Phase, IP65 RS Stock No: 725-5513



Product Details

RS Pro 11 kW automatic 3-phase DOL starter measures 110 x 148 mm. This enclosed, direct-on-line motor starter combines high performance and low cost. It includes options with and without isolator and support for motors from 5.5 kW to 11 kW. The options without isolator have space to mount additional 17.5 mm wide module such as a timer, level control or monitoring relay. The moulded plastic case provides IP65 ingress protection.

Features and Benefits

- Operating temperature range: -25 to +60°C
- Range available with and without isolator
- Voltage rating of 230 V ac
- 3 poles
- DOL starter
- Compliant with standards IEC/EN 60947-1 and IEC/EN 60947-4-1

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.



ENGLISH

Specifications:

Additional Features	Disconnect Switch Not Included
Enclosure	Yes
Motor Starter Functionality	Automatic
Motor Starter Type	DOL
Phase	3
Standards Met	RoHS Compliant; IEC/EN 60947-1; IEC/EN 60947-4-1
Overall Depth	148 mm
Overall Length	225 mm
Overall Width	110 mm
Current Rating	17 to 23 A
IP Rating	IP65
Number of Poles	3
Power Rating	11 kW
Voltage Rating	230 V ac
Motor Supporting Range	5.5 to 11 kW
Operating Temperature	-25 to +60°C