



Datasheet

Steel Zinc Plated J Hook, 13mm

RS Stock number 397-4904



Description:

Steel cup hook shouldered ZP 13mm

Specification:

Material: Steel

Finish: Zinc Plated


Dimensions: 2mm Dia. X 20mm

Overall Length, I.D.: 6mm

Package: 10pcs in polybag

Dimensions (mm)

A: 2.0 B: 6.0 C: 13.0 D: 7.0






ENGLISH

PAGE: 1/8


Item No.	Description	Dimension (MM)				
<u></u>		A	В	Ċ	D	
397-4904	Steel Cup Hook Shouldered ZP 13mm	2.0	6.0	13.0	7.0	
397-4910	Steel Cup Hook Shouldered BP 13mm	2.0	6.0	13.0	7.0	
397-4932	Brass Cup Hook Shouldered 13mm	2.0	6.0	13.0	7.0	
397-4926	Steel Cup Hook Shouldered PVC 20mm	2.4	10.0	20.0	11.0	



Item No.	Description		Dimension (MM)				
		A	В	C	D		
397-4960	Brass Square Hook Shouldered 13mm	2.0	7.0	13,0	7,0		
397-5424	Steel Square Hook Shouldered ZP 13mm	2.0	7.0	13.0	7.0		
397-5430	Steel Square Hook Shouldered BP 13mm	2.0	7.0	13.0	7.0		
397-4954	Steel Square Hook Shouldered BP 20mm	2.4	10,0	20.0	11.0		
397-5468	Steel Square Hook Shouldered PVC 20mm	2.4	10.0	20.0	11.0		
397-4948	" ZP 20mm	2.4	10.0	20.0	11.0		



Ite	m No.	Description	Dimension (MM)			
			Α	В	C	D
39	7-5418	Ceiling Hook Steel ZP 50mm	3.3	10.0	53.0	15.0



Item No.	Description	Dimension (MM)			
		Α	В	С	D
397-5446	Steel Screw Eye BP B1 (20MM)	2,0	6.0	20.0	8.0



Item No.	Description	Dimension (MM)			
<u></u>		Α	В	C	K
397-4796	Picture Hook ZP 10LB W/NAIL	6.5	22.0	10.5	4.0
397-4803	Picture Hook BP 10LB W/NAIL	6.5	22.0	10.5	4.0



Nail Size: 1.4mm x 3/4"



ENGLISH

397-4825 ANGLE DRIVE HOOK ZP 10LB W/Nail

397-4847 ANGLE DRIVE HOOK BP 10LB W/Nail

(Thickness: 0.6mm)

Nail Size: 2.0mmx3/4"

397-4853 ANGLE DRIVE HOOK DOUBLE ZP 40LB W/Nail

397-4869 ANGLE DRIVE HOOK DOUBLE BP 40LB W/Nail

(Thickness: 0.7mm)

Nail Size: 2.6mmx1"

18.8mm -20mm→ 30.5mm

6.03mm

397-4897 SUCTION HOOK 20MM

Suction Diameter: 21mm Height: 9mm Head Diameter: 7.5mm Height: 3.5mm Neck Diameter: 3.5mm Height: 1mm