



Data Sheet

TES-45

LAN CABLE TESTER

RS Stock No. 425-0754

FEATURES :

- Tests a wide range of FTP & UTP cables such as 10BaseT, 100BaseTx, 10Base2 (Coax), 356A, TIA-568A, TIA-568B, Token Ring, etc.
- Tests for wiring faults such as open, shorted, reversed, crossed and split wires.
- Identifies up to 8 different cables at one end with remote identifiers.
- Two large alphanumeric LED and 8 analogue pair LED clearly display fault status.
- Simple and practical to use.
- Over voltage (max.56V) is provided to prevent damage from miss connecting to live circuit of networking.
- Auto power off

SPECIFICATIONS :

Display/LEDs	Double digital 14-segment LED
	Four Fail (red) LEDs
	Four Pass (green) LEDs
Connector	RJ45, BNC
Cable pairs tested	1/2 , 3/6 , 4/5 , 7/8
Faults status	Open , Short , Reversed , Crossed , Split and Low Battery
Test cable length	Maximum : 150M (492ft)
Power	9Volt battery
Size	170x50x39mm
Weight	Approx. 180g
Environment Conditions	Operating : 0°C to +50°C
	Storage : -20°C to +60°C
Accessories	Instruction Manual, One Patch Cable (RJ-45 to RJ-45, 30cm long) & One Remote Identifier #1 (Optional for #2, #3 & #4).

