

Datasheet

## RS Pro 24V, 10A Lead Acid Battery Charger, EURO, UK Plug

RS Stock No: **549-322**



### Product Details

RS Pro lead acid battery charger is a high quality range of automatic charger with 3 stage controls. The charger yields 24 V output voltage at 10 A charge current. The EURO UK plug type charger has a charging current(s) of 2 to 25 A with many models provided in aluminium impact resistant casing and supplied with UK and EU mains leads and crocodile clip connectors. The battery charger meets RoHS and CE directive standards.

### Features and Benefits

- 3 stage control (fast/normal/float)
- Full charge with automatic shutdown
- Short circuit output protected
- Most models with 115/230 V input range
- Reverse polarity protected
- Overload protected
- UK/EU plugs
- LED indicator included
- Compliant to safety standards
- RoHS and CE directive compliant

**Specifications:**

Battery Type Charged	Lead Acid
Number of Charge Stages	3
Plug Type	EURO, UK
Standards Met	CE Certified; RoHS Compliant
User Interface	Indicator LEDs
Charge Current	10 A
Dimensions	210 x 186 x 76 mm
Input Current	15 A at 115 V ac, 7.5 A at 230 V ac
Input Voltage	115/230 V ac
Output Voltage	24 V
Output Voltage @ Charge Current	24 V at 10 A
Weight	2.4 kg
Input Frequency Range	47 to 63 Hz