



ENGLISH

Datasheet

RS Pro 12V, 10A Lead Acid Battery Charger, EU Plug

RS Stock No: **549-328**



Product Details

RS Pro lead acid battery charger is a high quality range of automatic charger with 3 stage controls. The charger yields 12 V output voltage at 10 A charge current. The EU plug type charger has a charging current(s) of 2 to 50 A with many models provided in aluminium impact resistant casing and supplied with UK and EU mains leads and crocodile clip connectors. The battery charger meets RoHS and CE directive standards.

Features and Benefits

- 3 stage control (fast/normal/float)
- Full charge with automatic shutdown
- Short circuit output protected
- Most models with 115/230 V input range
- Reverse polarity protected
- Overload protected
- UK/EU plugs
- LED indicator included
- Compliant to safety standards
- RoHS and CE directive compliant



ENGLISH

Specifications:

Battery Type Charged	Lead Acid
Number of Charge Stages	3
Plug Type	EU
Standards Met	CE Certified; RoHS Compliant
User Interface	Indicator LEDs
Charge Current	10 A
Dimensions	186 x 88 x 47.5 mm
Input Voltage	115/230 V ac
Output Voltage	12 V
Output Voltage @ Charge Current	12 V at 10 A
Weight	0.8 kg
Input Frequency Range	50/60 Hz