



ENGLISH

Datasheet

**RS Pro Cartridge Fuse, F, 0.25A, 5 x 20mm**

RS Stock No: **668-5953**



## Product Details

RS Pro cartridge fuse is current rated for 0.25 A. This F-speed, glass bodied fuse is ideal for protection of electrical circuits and consumer appliances.

**Specifications:**

Body Material	Glass
Breaking Capacity (at Maximum Voltage Rating)	35 A
Current Rating	0.25 A
Diameter	5.2 mm
Fuse Speed	F
High Rupture Capacity	No
Includes Indicator	No
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Operating Temperature Range	-55 to +125°C
Overall Dimensions	5.2 x 20 mm
Overall Length	20 mm
Resistance	2.3610 Ω
Size Designation	Miniature
Voltage Rating	250 V ac
Standards Met	CSA Certified, UL Listed, RoHS Compliant