

Datasheet

Steel Kick Step (Blue)

RS Part No. 669-3819

GS Approved

RAL No. RAL5002

Weight: 5Kg

Working load: 150 kgs

Overall Height: 400mm
Diameter (Top): 260mm
Diameter (Base): 430mm



Topstep provides easy step up access preventing excessive stretching.

The mobile step is supplied K/D where two sections permanently 'lock' together via a built-in bolt free mechanism.

- Topstep is the perfect accessory for any storeroom, office or workplace, where safe access is required for items stored at height.
- Mounted on retractable spring mounted castors Topstep can easily be moved into position without bending or lifting and when stepped on Topstep locks into position allowing safe access.
- Its sturdy steel construction with anti-slip rubber treads and base surround provide a solid platform from which to work.

