

Datasheet

Access Control Door Magnet, 2400lb DC, 12 V dc, 24 V dc

RS Stock number 741-8262

ELECTRIC LOCKING SYSTEMS

Double Standard Magnet

10040/60

- Operating Voltage: 12 or 24Vdc
- Brushed aluminium
- Current draw: 500mA at 12Vdc
250mA at 24Vdc (at temperature 20°C)
- Magnetic bond sensor monitor output remotely monitors the door lock or unlock status. (N.C. Output-Door opened; N.O. Output-door closed) (SPDT rated 3A at 12Vdc)
- Status LED lights
- Operating temperature: -10 to 55°C (14 to 131°F)
- Humidity: 0 to 95% non-condensing
- Lock's surface temperature: Current temperature ±20% (when power is on)
- Holding force: Up to 1200lbs x 2 (545kg x 2)
- Weight: 8.0kg (approx)



VARIATIONS	
10060	DbL. Standard Magnet
10060DS	DbL. Standard Magnet C/W Door Status
10040	DbL. Standard Monitored Magnet
10040DS	DbL. Standard Monitored Magnet C/W Door Status

All dimensions in mm

DIMENSIONS	LENGTH	WIDTH	DEPTH
Magnet	532	68	40
Armature Plate	185	62	16