

**ENGLISH** 

#### **Datasheet**

# RS Pro 500mA Axial FF Non-Resettable Wire Ended Fuse, 250 V ac

RS Stock No: 764-9576



#### **Product Details**

RS Pro axial non-resettable fuse withstands currents up to 500 mA. This wire-ended fuse offers FF speed with a voltage rating of 250 V ac. It has thermoplastic body for added durability. The very fast acting fuse forms a convenient and reliable solution to a vast array of application requirements.

#### **Features and Benefits**

- FF speed fuse
- Non-resettable
- Axial
- Wire-ended



## ENGLISH

### **Specifications:**

Body Diameter	3.18 mm
Body Height	7.1 mm
Body Material	Epoxy Coated
Breaking Capacity (at Maximum Voltage Rating)	50 A at 250 V ac
Current Rating	500 mA
Fuse Speed	FF
Lead Orientation	Axial
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Voltage Rating	250 V ac
Voltage Rating	250 V ac
Wire Diameter	0.64 mm
Wire Length	28 mm
Fuse Type	Very Fast Acting
Nominal Resistance	0.3734 Ω
Standards Met	TUV, RoHS