



Datasheet

ENGLISH

ELECTRIC LOCKING SYSTEMS

RS Door Retaining Magnets

RS Stock No.7748188

- Power input: 12Vdc or 24Vdc
- Voltage tolerance: $\pm 15\%$
- Current draw: 125mA at 12Vdc
60mA at 24Vdc (at temperature 20°C)
- Holding force: Up to 100lbs
- Over-ride switch
- Black powder-coat finish



DIMENSIONS	LENGTH	WIDTH	DEPTH
Lock	90	65	34
Armature Plate	65	65	44

All dimensions in mm