



Product Datasheet

ENGLISH

Hose Reel

With male fixed fitting (PT)

RS Stock No. 788-3732
RS Stock No. 788-3736
RS Stock No. 788-3739



PRODUCT FEATURES

- Heavy duty reinforced steel construction with powder paint coating.
- Automatic hose reel. Ratchet or free-running operation.
- Spring protector protects hose against damage when pulled and/or stretched.
- Supplied with wall/ceiling mounted bracket.
- Steel housing: powder painted heavy duty steel case protects retracted hose.
- Spring: strong steel spring automatically rewinds hose after catch is released.
- Stopper: can adjust the length of hose remaining outside the reel when retracted.
- High quality hose: polyurethane braid hose.
- Air inlet: brass coupling, 360° rotation.



ENGLISH

SPECIFICATION

Case Standard Color: Yellow

Hose Standard Color: Blue

Temperature Range: -5°C ~ +60°C

Article No	Hose ID	Hose Length (inlet)	Hose Length (outlet)	W.P	B.P	Thread Size (inlet+outlet)	Weight (N.W.)
788-3739	8mm	1M	10M	15bar	60bar	1/4"+1/4"	9kgs
788-3732	8mm	2M	10M	15bar	60bar	3/8"+3/8"	9kgs
788-3736	8mm	1M	15M	15bar	60bar	1/4"+1/4"	9kgs

Note:

1 pc / colour box