


SPEC	CIFICATIONS
HOUSING MATERIAL/COLOR	NYLON/BLACK
CONTACT MATERIAL/PLATING	BRASS/OPTALOY
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	125 V
MAXIMUM WIRE SIZE	18 AWG
CABLE GRIP RANGE	4–5mm
TEMPERATURE RANGE	-40°C to +85°C (-40°F to +185°F)
PROTECTION CLASS	MEETS IEC IP67





SOURCE DRAWING - FOR REFERENCE ONLY

	RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	High Technology	RCK Inc. Sensors and Automation Controls	(763) 553-7300		
	MATERIAL		DRFT RWC	DATE 03/01/06	DESCRIPTION DBSM 8151-	0		
	SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS	APVD	D SCALE 1=1.0		.0		
		DRAWING ARE FOR REFERENCE ONLY	UNIT OF ME	ASUREMENT	IDENTIFICATION NO.	REV		
	FINISH	CONTACT TURCK	MILLIMETER [INCH]		U0890-42			
3788	SEE SPECIFICATIONS	FOR MORE INFORMATION			00890-42	В		
D NO.					FILE: U0890-42	SHEET 1 OF 1		

					SEE	SPECIFIC
					FINISH	
В	UPDATE SPECIFICATIONS	NF	03/15/16	53788	SEE	SPECIFIC
REV	DESCRIPTION	BY	DATE	ECO NO.		