TURCK M12 eurofast Connectivity

4 and 5-Wire Receptacles, Rear Mount with Leads



- NEMA 1, 3, 4, 6P
- IEC IP68 Protection
- 250 V, 4 A (4 & 5 pole)
- 60 VAC/75 VDC, 2A (6 pole)



FL

Housing Style	Female Part Number	Male Part Number	Features		Pinout
FKFD118 [3.0] MAX —	FKFD 4.4-*	FSFD 4.4-*	4x22 AWG, 105°C, mates with 4-pin cordsets	1. BN 2. WH 3. BU 4. BK	Female 3 2
	FKFD 4.4-*/\$621	FSFD 4.4-*/S621	4x18 AWG, 105°C, mates with 4-pin cordsets	1. GY1 2. GY2 3. GY3 4. GY4	Male 1
FSFD* .118 [3.0] MAX PG 9 .118 [3.0] MAX Typical panel cutout is 15.3 x 14 mm.	FKFD 4.5-*	FSFD 4.5-*	5x22 AWG, 105°C, mates with 5-pin cordsets	1. BN 2. WH 3. BU 4. BK 5. GY	Female 5 3
	FKFD 4.5-2/S653	FSFD 4.5-2/S653	4x22 AWG, Drain, 105°C, 5.1 mm OD, mates with 5-pin cordsets, 4 Conductors PVC Foil Shielded with Drain Wire to pin 5	1. BN 2. WH 3. BU 4. BK 5. Drain	Male 5 000 2
	FKFD 6-*	FSFD 6-*	UL, CSA, 6x24 AWG, 105°C, mates with 6-pin cordsets	1. BN 2. WH 3. BU 4. BK 5. GY 6. PK	Female 5 4 00 1 Male 6 6 2 3 2

^{*} Length in meters. Standard lead length is 0.5 meters. Consult factory for other lengths. Standard housing material is nickel plated brass "FSFD.."; "FSFDV.." indicates stainless steel. To specify PVC jacketed cable, add "/S717" to the end of the part number.