

Cable-cutting tool - CUTFOX 10 - 1206829

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Automatic cutting device for cables, litz wires, and shrink sleeves, for 100 - 240 V mains voltage

Why buy this product

- The desired length and number is entered via the user-friendly display
- The drive and guide rolls automatically adjust to each inserted diameter
- The cutting machine cuts conductors, cables, and similar profiles
- No adjustments are required thanks to the automatic zero cut, which is performed when the start button is pressed
- To insert the conductors simply open the front cover

Key Commercial Data

Packing unit	1 STK
GTIN	 4 017918 178871
GTIN	4017918178871

Technical data

Dimensions

Length (b)	301 mm
Width (a)	194 mm
Height (c)	228 mm
Stripping length	6 mm

General

Note	Cutting efficiency
Power consumption	150 VA
Maximum throughput	8
Cross section setting	automatic
Section length	2 mm ... 999999 mm
Maximum number of cuts	9999

Cable-cutting tool - CUTFOX 10 - 1206829

Technical data

General

Feed rate	0.5 m/s
Host system interface	RS-232
Dialog language	German / English / French / Italian
Minimum stripping length	2 mm
Maximum stripping length	999999 mm
Weight	11 kg
Min. cross section	0.08 mm ²
Max. cross section	10 mm ²

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>