


passive junction
CANopen/DeviceNet Junction Box
JBBS-57-E411



- Housing material: Nylon
- Housing color: black
- Protection class IP67
- RoHS-compliant
- CE compliant
- All pins are connected through (1:1)
- The DeviceNet™ supply voltage between pin 2 and 3 (11 ... 30VDC) is displayed via an LED In CANopen this supply voltage is optional.
- Passive junction, 4-port
- Protection class IP67
- 1 × M12 male connector
- 4 × M12 female connector

Type	JBBS-57-E411
ID	6603378
Housing	Plastic, PA, Black
I/O Port	Female, M12 × 1
Number of contacts	5
Contact carriers	Plastic, PA, Black
Homerun connector	Male, M12 × 1
Number of contacts	5
Fieldbus	DeviceNet
Electrical properties at +20 °C	
Rated voltage	30VV
Current	Max. 4 A
Mechanical and chemical properties	
Ambient temperature range (static)	25°C...+60°C°C
Ambient temperature range (dynamic)	-25°C...+70°C°C

