

Components of electronic housing - UM-PRO 122 COVER-R BK - 2200159

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Lateral element (right) with mounting foot for DIN rails for UM-PRO profiles for PCB the width of 108 mm




Why buy this product

- Item is from the UM-BASIC/UM-PRO product range
- PVC press-drawn section (UM-BASIC) or PA (UM-PRO)
- Available in individual lengths
- Available in the overall widths of 72 mm, 108 mm, and 122 mm
- Variety of connection technologies
- Can be mounted on the DIN rail



Key Commercial Data

Packing unit	10 STK
GTIN	 4 046356 547413
GTIN	4046356547413

Technical data

General

Housing type	Panel mounting base
Housing material	Polyamide
Color (RAL)	black

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

Dimensions

Length	15.5 mm
Constructional height	40 mm

Components of electronic housing - UM-PRO 122 COVER-R BK - 2200159

Technical data

Dimensions

Width	142.3 mm
-------	----------

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Approvals

Approvals

Approvals

UL Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 240868
---------------	---	---	---------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>