



Powering Business Worldwide

1547-70-P

GROMMET 20/30 AMP BLK .360-.425 Bag of 5

UPC: 032664733710

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: (2) Power Outlet

Size: Standard, 4.56 In Width X 4.50 In Height

Gang: 2

Material: Chrome

Mounting: Screw

1547-71-P

GROMMET 20/30 AMP BLU .425-.520 Bag of 5

UPC: 032664733727

Brand Name: Cooper Wiring Devices

Type: Screw

Special Features:

Application: Toggle Switch and Receptacle Wallplate

Size: #6-32 TPI X 1/2 In

Color: Brown

1547-72-P

GROMMET 20/30 AMP RED .520-.620 Bag of 5

UPC: 032664733734

Brand Name: Cooper Wiring Devices

Type: Screw

Special Features:

Application: Toggle Switch and Receptacle Wallplate

Size: #6-32 TPI X 1/2 In

Color: Ivory

1547-73-P

GROMMET 20/30 AMP NAT .620-.720 Bag of 5

UPC: 032664733741

Brand Name: Cooper Wiring Devices

Type: Screw

Special Features:

Application: Toggle Switch and Receptacle Wallplate

Size: #6-32 TPI X 1/2 In

Color: White



Powering Business Worldwide

1547-74-P

GROMMET 20/30 AMP GRN .720-.820 Bag of 5

UPC: 032664733758

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Screw

Special Features: Toggle Switch and Receptacle Wallplate

Application: Toggle Switch and Receptacle Wallplate

Size: #6-32 TPI X 1/2 In

Gang: 0

Cutout: 0.40 In Width X 0.93 In Height

Material: Nylon

Color: Ivory

Mounting: screw

Construction: Wallplate

1547-75BK-P

GROMMET 20/30 AMP BLK .820-.930 Bag of 5

UPC: 032664733765

Brand Name: Cooper Wiring Devices

Type: Screw

Special Features:

Application: Toggle Switch and Receptacle Wallplate

Size: #6-32 TPI X 1/2 In

Material: Nylon

Color: White

1547-75-P

GROMMET 20/30 AMP YEL .820-.930 Bag of 5

UPC: 032664733772

Brand Name: Cooper Wiring Devices

Type: Duplex, Straight Blade

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Vinyl Body, Solid Brass Plug Blades

Color: Ivory

NEMA Rating: 5-15R

Connection: Screw



Powering Business Worldwide

1547-76-P

GROMMET 20/30 AMP ORG .930-1.05 Bag of 5

UPC: 032664733789

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Lampholders

Special Features: Wattage 75 W, Size 0.68 In Diameter X 0.98 In Height

Application: Electrical Equipment, Harnesses, Light Strings

Standard: UL

Voltage Rating: 125 Vac

Amperage Rating: 75 Watts

Base: Miniature

Connection: 5 In Pigtail Lead

Material: Phenolic

Color: White

Mounting: Screw

1547-77-P

GROMMET 20/30 AMP GRY 1.05-1.15 Bag of 5

UPC: 032664733796

Brand Name: Cooper Wiring Devices

Type: Connector

Special Features: Finish Brass, For Ball Chain

Application: Lampholder