



The Stinger Classic LED was designed to replicate the size, shape and feel that you loved so much about the original model enhanced with current LED technology.

Material/ Lens Anodized aluminum construction with knurled barrel for a sure grip. Custom acrylic optic

Dims/Weight Length: 7.65 in. (19.43 cm); Diameter: Major Diameter: 1.60 in. (4.06 cm); Body Diameter: 1.08 in. (2.74 cm); Weight 11.1 oz (315 grams) with battery

Light Source C4® LED technology, shock-proof with a 50,000 hour lifetime. Optimized custom optic design provides a smooth beam with optimal peripheral illumination. Regulated run time provides consistent performance throughout battery life

Three modes and strobe:

- High for a super-bright, far-reaching beam: 390 lumens; 13,200 candela; 230m beam; runs 1.75 hours
- Medium for bright light and longer run times: 210 lumens; 6,500 candela; 161m beam; runs 3.75 hours
- Low for light without glare and extended run times: 100 lumens; 3,100 candela; 111m beam; runs 6.75 hours
- Strobe for disorienting or signaling your location: runs 5 hours

Switch Multi-function, easy access push-button switch designed for extremely long life; tested at 1 million actuations. Access high, medium, low and strobe

Battery 3-Cell, 3.6-Volt Nickel-cadmium sub-C battery is rechargeable up to 1000 times
 3-cell, 3.6 Volt Ni-MH sub-C battery, rechargeable up to 1000 times

Charging Steady charger: Fully recharges within 16 hours
 Smart charger: Fully recharges within 4.5 hours (5V/1A USB input) or 3 hours (12VDC input)
 Smart PB charger: Fully recharges within 7.5 hours (5V/1A USB input) or 4 hours (12VDC input)

Features

- LED charge-continuity indicator, compact
- 1 meter impact resistance tested
- IPX4 Rated for water resistant operation
- Snap-in charger holder that mounts in any position
- Serialized for positive identification

Approvals Most models meet applicable European Community Directives

Warranty Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item Description	UPC	Item #
Stinger Classic LED - IEC Type C (230V) AC/12V DC - 2 Holders (NiMH)	080926-75672-4	75672
Stinger Classic LED - IEC Type G (240V) AC/12V DC - 2 Holders (NiMH)	080926-75680-9	75680
Stinger Classic LED - IEC Type A (120V) AC/12V DC - 2 Holders Smart Charge (NiCd)	080926-75662-5	75662
Stinger Classic LED - IEC Type A (100V) AC/12V DC - 2 Holders (NiMH)	080926-75667-0	75667
Stinger Classic LED - IEC Type C (230V) AC (NiMH)	080926-75674-8	75674
Stinger Classic LED - IEC Type G (240V) AC (NiMH)	080926-75681-6	75681
Stinger Classic LED - IEC Type A (120V) AC Smart Charge (NiCd)	080926-75663-2	75663
Stinger Classic LED - IEC Type A (100V) AC (NiMH)	080926-75668-7	75668
Stinger Classic LED - 12V DC Smart Charge (NiMH)	080926-75675-5	75675
Stinger Classic LED - IEC Type A (120V) AC/12V DC Smart Charge PiggyBack (NiCd)	080926-75666-3	75666
Stinger Classic LED - (WITHOUT CHARGER) (NiMH)	080926-75661-8	75661



Item	UPC	Item #
DC2 direct wire charge cord	080926-22050-8	22050
DC1 Charge Cord	080926-22051-5	22051
120V AC USB Dedicated Charge cord	080926-22071-3	22071
230V AC USB Dedicated Charge cord	080926-22072-0	22072
240V AC USB	080926-22049-2	22049
IEC Type A (100V/120V) AC charge cord	080926-22060-7	22060
Type C (230V) AC charge cord	080926-22061-4	22061
Type G (240V) AC charge cord	080926-22062-1	22062
Smart Charger Holder	080926-75015-7	75105
Smart PiggyBack® Charger Holder & Battery	080926-75277-1	75277
5 Unit Bank Charger, 120V	080926-75400-3	75400
5 Unit Bank Charger, 230V	080926-75600-7	75600
Battery Stick (NiCd)	080926-75175-0	75175
Battery Stick (NiMH)	080926-75375-4	75375
Battery Stick (Lithium Ion)	080926-75176-7	75176

Item	UPC	Item #	
Flip Lens	IR	080926-75027-2	75027
Flip Lens	Red	080926-75115-6	75115
Flip Lens	Blue	080926-75116-3	75116
Flip Lens	Green	080926-75117-0	75117
Safety Wand	Blue	080926-75902-2	75902
Safety Wand	Red	080926-75903-9	75903
Safety Wand	Yellow	080926-75904-6	75904
Safety Wand	White	080926-75908-4	75908
Safety Wand	Glow in the Dark	080926-75913-8	75913
Ring Holder		080926-75906-0	75906
Duty Holster		080926-88053-5	88053
Holster		080926-75927-5	75927
Loop holster		080926-75928-8	75928
Leather holster: Plain - Stinger LED/PolyStinger LED		080926-75133-0	75133
Leather holster: Basket Weave - Stinger LED/ PolyStinger LED Series		080926-75134-7	75134

