STRION® LED RECHARGEABLE FLASHLIGHT

FL1 STANDARD	HIGH	MEDIUM	LOW
31/5	260 LUMENS	130 LUMENS	65 LUMENS
0	2h	4h	7h 30min
	200m	141m	100m
	10,000cd	5,000cd	2,500cd



Strobe runs 5.5 hours

Case Material 6000 series machined aircraft aluminum with anodized finish

Dimensions Length: 5.90 in. (14.99 cm) Head Diameter: 1.25 in. (3.18 cm) Head Diameter at Tri-Lobe Anti-Roll Flange: 1.44 in. (3.66 cm) Barrel Diameter: 0.95 in. (2.41 cm)

Weight 5.22 oz (148 grams) with battery

Lens Borofloat high temperature glass lens

Light Source C4® LED technology, impervious to shock with a 50,000 hour lifetime.

Switch Multi-function, push-button tactical tailswitch. One handed operation of momentary, variable intensity or strobe mode.

Output/Runtime: Three modes and strobe:

- High for a bright super-bright beam - 260 lumens; 10,000 candela peak beam intensity; 200 meter beam distance; runs 2 hours

- Medium for bright light and longer run times - 130 lumens; 5,000 candela peak beam intensity; 141 meter beam distance; runs 4 hours

- Low for light without glare and extended run times - 65 lumens; 2,500 candela peak beam intensity; 100 meter beam distance; runs 7.5 hours

- Strobe for disorienting or signaling your location; runs 5.5 hours

Battery Lithium Ion with on-board safety control circuit, 3.75V, 2200mAh, rechargeable up to 1000 times

Charging Clamp style charge holder with digital control circuit that prevents over charge. Fully recharges battery in 3 hours. Charge base LED indication: LED Steady – Charging; LED Blinking – Charged. Standard or PiggyBack® charger

Features • C4 LED technology for extreme brightness

· LED Charge-continuity indicator on charger base; Compact, snap-in charger mounts in any position

IPX4 water resistant operation; 2 meter impact resistance tested

Serialized for positive identification

Approvals Most models meet applicable European Community Directives

Warranty Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Description	Item #	UPC
Strion LED with Type C (230V) AC/DC 1 Holder	74311	080926-74311-3
Strion LED with 240V AC/DC 1 Holder	74321	080926-74321-2
Strion LED with Type A (100V/120V) AC/DC 1 Holder	74301	080926-74301-4
Strion LED with Type A (100V/120V) AC/DC 1 Holder - Clam	74308	080926-74308-3
Strion LED with Type C (230V) AC/DC 2 Holders	74312	080926-74312-0
Strion LED with 240V AC/DC 2 Holders	74322	080926-74322-9
Strion LED with Type A (100V/120V) AC/DC 2 Holders	74302	080926-74302-1
Strion LED with Type A (100V/120V) AC/DC PiggyBack	74353	080926-74353-3
Strion LED with Type A (100V/120V) AC/DC PiggyBack - Kryptek®	74369	080926-74369-4

Description	Item #	UPC		
Strion LED with Type C (230V)	74313	080926-74313-7		
Strion LED with 240V AC	74323	080926-74323-6		
Strion LED with Type A (100V/120V) AC	74303	080926-74303-8		
Strion LED with Type A (100V/120V) AC with grip ring	74303	080926-74303-8		
Strion LED with DC	74309	080926-74309-0		
Strion LED (Without Charger)	74300	080926-74300-7		
Strion LED (Without Charger) - Kryptek®	74368	080926-74368-7		
Additional part numbers on reverse				

Assembled in USA

All Rights Reserved. Kryptek® is a registered trademark of Kryptek Outdoor Group, LLC. Streamlight has not sought endorsement of this product from Kryptek Outdoor Group, LLC.













