





STRION® HPL™ RECHARGEABLE FLASHLIGHT

FL1 STANDARD	HIGH	MEDIUM	LOW
	615 LUMENS	320 LUMENS	160 LUMENS
	1h	2h	3h 45min
	400m	283m	200m
	40,000cd	20,000cd	10,000cd

Strobe runs 2.5 hours



This long-range flashlight shines farther at 400 meters with 40,000 candela.

Case Material 6000 series machined aircraft aluminum with anodized finish

Dimensions Length: 7.00 in (17.78 cm) Major Diameter: 2.20 in. (5.59 cm) Barrel Diameter: 0.95 in. (2.41 cm)

Weight 7.1 oz (202 grams) with battery

Lens Unbreakable polycarbonate lens with scratch-resistant coating. O-ring sealed

Light Source C4® LED technology, impervious to shock with a 50,000 hour lifetime.

Switch Multi-function, push-button tactical tailswitch. One handed operation of momentary, variable intensity or strobe mode.

Output/Run Four operating modes:

- High for a high-lumen, far-reaching beam: 615 lumens; 40,000 candela; 400m beam; runs 1 hours
- Medium for bright light, good beam distance and longer run time: 320 lumens; 20,000 candela; 283m beam; runs 2 hours
- Low provides a less intense beam and extended run time: 160 lumens; 10,000 candela; 200m beam; runs 3.75 hours
- Strobe for disorienting or signaling: runs 2.5 hours

Battery Lithium Ion with on-board safety control circuit, 3.75V, 2000mAh minimum, rechargeable up to 1,000 times.

Charging Clamp style charge holder with digital control circuit that prevents over charge. Fully recharges battery in 3 hours. Charge base LED indication: LED Steady – Charging; LED Blinking – Charged. Standard or PiggyBack® charger

- Features
- C4 LED technology for extreme brightness
 - LED Charge-continuity indicator on charger base; Compact, snap-in charger mounts in any position
 - IPX4 water resistant operation; 2 meter impact resistance tested
 - Serialized for positive identification

Approvals Most models meet applicable European Community Directives

Warranty Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item	UPC	Part #
Strion HPL Type C (230V) AC/12V DC (1) Holder	080926-74511-7	74511
Strion HPL 240V AC/12V DC (1) Holder	080926-74521-6	74521
Strion HPL Type A (100V/120V) AC/12V DC (1) Holder	080926-74501-8	74501
Strion HPL Type C (230V) AC/12V DC (2) Holder	080926-74512-4	74512
Strion HPL 240V AC/12V DC (2) Holder	080926-74522-3	74522
Strion HPL Type A (100V/120V) AC/12V DC (2) Holder	080926-74502-5	74502
Strion HPL Type A (100V/120V) AC/12V DC PiggyBack	080926-74536-0	74536

Item	UPC	Part #
Strion HPL Type C (230V)	080926-74513-1	74513
Strion HPL 240V AC	080926-74523-0	74523
Strion HPL Type A (100V/120V) AC	080926-74503-2	74503
Strion HPL 12V DC	080926-74504-9	74504
Strion HPL (WITHOUT CHARGER)	080926-74500-1	74500
See reverse for additional part numbers		

Assembled in USA



Item	UPC	Part #
DC2 direct wire charge cord	080926-22050-8	22050
DC1 Charge Cord	080926-22051-5	22051
120V AC charge cord	080926-22311-0	22311
100V AC charge cord	080926-22666-1	22666
Type C (230V) AC charge cord	080926-22061-4	22061
240V AC charge cord	080926-22241-0	22241
USB A to Micro (Custom) Cord	080926-22070-6	22070
Intl AC USB Wall Plug	080926-22059-1	22059
6-unit Bank Charger 120V AC	080926-74400-4	74400
USB Charger Holder	080926-74114-0	74114
PiggyBack Charger (cords and battery not included)	080926-74115-7	74115
Bank Charger 120V AC	080926-74400-4	74400
Bank Charger 230V AC	080926-74600-8	74600
Bank Charger 12V DC	080926-74401-1	74401
Battery Stick (Li-Ion)	080926-74175-1	74175
Rail Mount	080926-74200-0	74200
Vertical Grip with Rail - machined aluminum, ambidextrous hard anodized rail grabber vertical foregrip with integral Picatinny rail and storage compartment	080926-69114-8	69114
Safety Wand Red	080926-75946-6	75946
Safety Wand Blue	080926-75947-3	75947
Safety Wand Yellow	080926-75948-0	75948
Safety Wand White	080926-75949-7	75949
Safety Wand Glow in the dark	080926-75950-3	75950
Tactical Holster	080926-88051-1	88051
Nylon Holster	080926-75910-7	75910