4AA ProPolymer® Lux DIV 1/DIV 2 Alkaline Battery-Powered Flashlight



- Case Engineering polymer resin that is virtually indestructible, shock resistant, non-conductive and light weight. Unbreakable polycarbonate lens with Material/Lens: scratch-resistant coating
- Dimensions/ Length: 7.00 in. (17.78 cm) Body thickness: 0.97 in. (2.46 cm) Width: 1.35 in. (3.43 cm) Facecap diameter: 1.69 in. (4.29 cm) Body Diameter: 1.48 in. (3.76 cm) Weight: Weight: 7.6 oz (216 grams) with batteries
- Light Source: C4[®] LED technology, impervious to shock with a 50,000 hour lifetime. Deep parabolic reflector produces long-range brilliance and smooth uniform beam pattern.Optimized electronics provide maximum light output throughout battery life.
- Output/Run Time: 100 lumens; 4,200 candela; 130m beam; runs 6 hours

On/Off: Push button tail switch provides one handed momentary or constant operation

Battery: Four "AA" alkaline batteries (included)

- Features: IP67 rated design; waterproof to 1 meter for 30 minutes
 - 1 meter impact resistance tested
 - Non-conductive
 - Corrosion proof
- Approvals: Most models meet applicable European Community Directives.

DIVISION 1:

UL Listed Class I, Division 1, Groups C & D; Class I, Division 2, Groups A,B,C,D;Class II, Division 1, Groups F & G; Class III; Exia; Temperature Code T4 MSHA: Permissible Flashlight; Approval No.20-A060002-0;Tested for use in Methane-Air mixtures only

DIVISION 2:

UL Listed Class I, Division 2, Groups A, B, C & D; Class II, Division 2, Groups F & G; Class III; Temperature Code T3C

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item		UPC	Part #		
4AA ProPolymer Lux with alkaline batteries. Div 2	Yellow	080926-68244-3	68244		
4AA ProPolymer Lux with alkaline batteries. Div 2	Black	080926-68344-0	68344		
4AA ProPolymer Lux with alkaline batteries. Div 1	Yellow	080926-68602-1	68602		
4AA ProPolymer Lux with alkaline batteries. Div 1	Black	080926-68702-8	68702		
See back for accessories					









Helmet Strap. Helmet and light not included.



Gallet Mount



Helmet Mount

Item		UPC	Part #
Nylon Holster		080926-68905-3	68905
Safety Wand	Yellow	080926-75904-6	75904
Safety Wand	Red	080926-75903-9	75903
Safety Wand	Blue	080926-75902-2	75902
Safety Wand	White	080926-75908-4	75908
Safety Wand	Glow-in-the-dark	080926-75913-8	75913
Rubber Helmet Strap		080926-99075-3	99075
Poly Mount		080926-68089-0	68089
3AA/4AA Helmet Mount		080926-68085-2	68085
3AA/4AA Gallet Helmet Mount		080926-68086-9	68086
3AA/4AA Gallet Helmet Mount (fits Gallet F1S, F1SF, F2)		080926-68130-9	68130

