Twin-Task[®] 1L LED Flashlight



Case Material: Machined aluminum case with non-slip knurled grip and a matte black anodized finish

- Dimensions: Length: 4.09 in. (10.39 cm) Major Diameter: 1.33 in. (3.38 cm) Body Diameter: 0.98 in. (2.49)
 - Weight: 4.1 oz (115 grams) with battery (included with purchase)
 - Lens: Unbreakable polycarbonate lens.
- Light Source: C4® LED technology, impervious to shock with a 50,000 hour lifetime. Three (3) ultra bright white LEDs with 100,000 hour lifetime.
 - On/Off: Push button head switch sequences through C4® LED, Three ultra bright LEDs, C4 LED and Off
 - Battery: One 3V CR123A lithium battery.
 - Features: IPX4 rated for water resistant operation. All openings o-ring sealed 1 meter impact resistance tested
 - Approvals: Meets applicable European Community Directives
 - Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction
 - * With batteries (Included in purchase) Made in China



Item		UPC	Part #
Twin-Task 1L LED	Black	080926-51036-4	51036
Lithium batteries (2) Pack		080926-85175-7	85175
Lithium batteries (6) Pack		080926-85180-1	85180
Lithium batteries (12) Pack		080926-85177-1	85177
Lithium batteries (400) Pack		080926-85179-5	85179

