SIDEWINDER[®] ARTICULATING HEAD FLASHLIGHT



Case Material: High impact super-tough nylon case offers exceptional durability and weather resistance. All openings are O-ring sealed. Available in Coyote. Unbreakable polycarbonate lens with scratch-resistant coating. Gasket sealed.

Dims/Weight: Length: 2.34 in (4.94 cm) Width: 1.08 in. (2.74 cm) Depth: 4.65 in. (11.81 cm); 4.38 oz (124 grams) 5.02 oz (142 grams) with "AA" batteries

Light Source: High output white C4[®]LED, shockproof, 50,000Hr lifetime/55 lumens, 1,175 candela peak beam intensity and 69m beam distance

(See model for 5mm IR LED, 880 nm peak wavelength, shockproof, 100,000Hr lifetime/25mW/sr (min) radiant intensity

specific LED 5mm Red LED, 630 nm peak wavelength, shockproof, 100,000Hr lifetime/1 lumen, 40 candela peak beam intensity and 13m beam distance 5mm Blue LED, 470 nm peak wavelength, shockproof, 100,000Hr lifetime/1.8 lumens, 130 candela peak beam intensity and 23m beam distance 5mm Green LED, 527 nm peak wavelength, shockproof, 100,000Hr lifetime/4.5 lumens, 68 candela peak beam intensity and 16m beam distance

On/Off/Intensity Compound On-Off mode selector switch ergonomically separates On-Off-Dimming-Strobe and LED selection functions. Design does not require the operator to access separate switching locations on the device. Rubber dome actuator and 4 position pull-to-turn locking rotary selector knob with tactile indicator (IR for Miltary and Aviation models; green LED for Sportsman model) provides easy

Battery: Two (2) "AA" size alkaline batteryes (included) provide fast replacement with readily available batteries. Lithium "AA" cells allow extended operation in extreme temperature environments (-40F to 150F). Tactile battery polarity indication on body allows replacement of cells in dark environment.

SIDEWINDER® LIGHT OUTPUT & BATTERY RUN TIME								
LED	Light Output	Low 5% Output	Medium 1 25% Output	Medium 2 60% Output	High 100% Output	Strobe 100% Output		
C4*	55 Lumens	100 Hrs+	45 Hrs	11 Hrs	5.5 Hrs	10 Hrs		
5mm IR	25mW/sr (min) radiant intensity	200 Hrs+	140 Hrs	60 Hrs	24 Hrs	40 Hrs		
5mm Red	1 Lumens	200 Hrs+	140 Hrs	60 Hrs	24 Hrs	40 Hrs		
5mm Blue	1.8 Lumens	150 Hrs+	100 Hrs	35 Hrs	16 Hrs	30 Hrs		
5mm Green	4.5 Lumens	150 Hrs+	100 Hrs	35 Hrs	16 Hrs	30 Hrs		
All runtime claims to 10% of initial output level. Illumination output electronically regulated.								

Approvals: Most models meet applicable European Community Directives.

operation even when wearing heavy gloves.

Warranty: Streamlight warrants its Sidewinder (excepting batteries) will be free from

manufacturing defects under normal use for 12 months after purchase. During the warranty period, at its sole discretion, Streamlight will repair or replace any defective part or product

Features:	Push-button switch specified to 300K operations	Cord attachment holes provided in battery compartment cover capable of supporting		
	Pull-to-turn locking rotary knob prevents accidental mode changes	25 lbs of load		
		Tactile battery polarity indicators for battery replacement in the dark		
		Tethered battery compartment cap facilitates battery replacement in the dark without losing cap		
		IPX7 Rated design; waterproof to 1 meter for 30 minutes. Meets MIL-STD-801F Method 512.4		

Item Description	UPC	Part #	NSN
Sidewinder Military Model White C4 LED, Red, Blue, IR LEDs.			
Includes 2 "AA" alkaline batteries. Clam packaged	080926-14000-4	14000	6230-01-556-0487
Sidewinder Military Model White C4 LED, Red, Blue, IR LEDs.			
Includes 2 "AA" alkaline batteries. Boxed	080926-14032-5	14032	6230-01-571-1331
Sidewinder Military Model White C4 LED, Red, Blue, IR LEDs.			
Includes helmet mount and 2 "AA" alkaline batteries. Clam packaged	080926-14027-1	14027	6230-01-571-8752
Sidewinder Aviation Model White C4 LED, Green, Blue, IR LEDs.			
Includes 2 "AA" alkaline batteries. Clam packaged	080926-14008-0	14008	
Sidewinder Aviation Model White C4 LED, Green, Blue, IR LEDs			
Includes MOLLE retainer and 2 "AA" alkaline batteries. Boxed	080926-14024-0	14024	6230-01-572-6216





Item	UPC	Part #	NSN
Sidewinder Helmet Mount Coyote	080926-14055-4	14055	5340-01-576-8599
Safety Wand Glow-in-the-Dark	080926-14902-1	14902	
Replacement MOLLE retainer	080926-14030-1	14030	
1913 rail mount adapter (for helmets only. Not intended for use with long guns) Coyote	080926-14057-8	14057	8470-01-633-3396
Lithium batteries - 2 Pack	080926-85175-7	85175	
Lithium batteries - 12 Pack	080926-85177-1	85177	
Lithium batteries - 400 Pack	080926-85179-5	85179	
Lithium batteries - 6 Pack	080926-85180-1	85180	

