
Sidewinder® Rescue Personal Distress Marker





A slim, lightweight personal light that can be used as a life-saving beacon in times of distress or during swift water rescue operations.

Case Material: High impact super-tough nylon case offers exceptional durability and weather resistance. All openings are O-ring sealed. Available in Coyote. Unbreakable polycarbonate lens with scratch-resistant coating. Gasket sealed.

Length: 2.34 in (4.94 cm) Width: 1.08 in. (2.74 cm) Depth: 4.65 in. (11.81 cm); 4.38 oz (124 grams) 5.02 oz (142 grams) with "AA" batteries Dims/Weight:

Light Source/ Output/Runtime:

LEDs provide all of the colors you need for a distress marker - no need to use filters that can get lost or broken

- White C4® LED for bright light: 55 lumens; 1,175 candela; 69m beam distance

- Blue LED alerts friendly forces; distinguishes strobe from ground fire: 1.8 lumens; 130 candela; 23m beam distance

- IR LED for covert operations: 25mW/sr (min) radiant intensity

- Green LED to help preserve night vision: 4.5 lumens; 68 candela; 16m beam distance

All LEDs provide unidirectional light for general lighting needs and omni-directional light when using the diffuser

LED Color	Low	Medium 1	Medium 2	High	Strobe (100% output)
White C4 LED	100+ hours	45 hours	11 hours	5.5 hours	10 hours
Blue	150+ hours	100 hours	35 hours	16 hours	30 hours
IR	200+ hours	140 hours	60 hours	24 hours	40 hours
Green	150+ hours	100 hours	35 hours	16 hours	30 hours

Flash rate: 120 bpm (default); push and hold button to achieve 50 bpm

On/Off/Intensity Mode Selection: Compound On-Off mode selector switch ergonomically separates On-Off-Dimming-Strobe and LED selection functions. Rubber dome actuator and 4 position pull-to-turn locking rotary selector knob with tactile indicator is easy to operate even when wearing heavy gloves.

Two "AA" size alkaline batteryes (included) provide fast replacement with readily available batteries. Lithium "AA" cells allow extended operation in extreme temperature Battery: environments (-40F to 150F). Tactile battery polarity indication on body allows replacement of cells in dark environment.

Approvals: Most models meet applicable European Community Directives.

Streamlight warrants its Sidewinder (excepting batteries) will be free from manufacturing defects under normal use for 12 months after purchase. During the warranty period, at its sole discretion, Streamlight will repair or replace any defective part or product

- Diffuser provides omnidirectional light per CID A-A-59176 (formerly MIL-SPEC MIL-L-38217D)

- Aluminum plate provides flat surface to adhere Velcro® for attaching to helmet

- Paracord lanvard provides extra security from loss of the light and also allows it to be worn around the neck. Additionally, it can enhance air-to-ground visibility when the light is turned on and spun overhead like a lasso in a circular pattern to increase the likelihood of being spotted by a search and rescue team

- IPX7 Rated design; waterproof to 1 meter for 30 minutes. Meets MIL-STD-801F Method 512.4

Item Description	UPC	Part #
Sidewinder Rescue Kit - White C4 LED, Green, Blue, IR LEDs Includes MOLLE retainer, paracord and 2 "AA" alkaline batteries. Boxed	080926-14065-3	14065
Sidewinder Rescue Kit - White C4 LED, Green, Blue, IR LEDs Includes MOLLE retainer, paracord and 2 "AA" alkaline batteries. Clam	080926-14069-1	14069
Sidewinder Rescue - White C4 LED, Green, Blue, IR LEDs. Includes 2 "AA" alkaline batteries. Box	080926-14066-0	14066
Sidewinder Rescue - White C4 LED, Green, Blue, IR LEDs. Includes 2 "AA" alkaline batteries. Clam packaged.	080926-14067-7	14067
Sidewinder Rescue - White C4 LED, Green, Blue, IR LEDs. Includes E-mount and 2 "AA" alkaline batteries. Box	080926-14068-4	14068











Item	UPC	Part #	NSN
Sidewinder Helmet Mount Coyote	080926-14055-4	14055	5340-01-576-8599
Sidewinder Helmet Mount Green	080926-14056-1	14056	
Safety Wand Glow-in-the-Dark	080926-14902-1	14902	
Replacement MOLLE retainer	080926-14030-1	14030	
1913 rail mount adapter (for helmets only. Not intended for use with long guns) Coyote	080926-14057-8	14057	
1913 rail mount adapter (for helmets only. Not intended for use with long guns) Green	080926-14058-5	14055	
Sidewinder Helmet Mount Accessory Kit	080926-14112-4	14112	
Sidewinder Rail Mount Accessory Kit	080926-14113-1	14113	
NVG Mount (works with HGU-84 rotary wing aircrew helmet)	080926-14135-3	14135	
Sidewinder E-Mount Kit (ACH, ECH, MICH, LWH compatible)	080926-14136-0	14136	
Sidewinder E-Mount Accessory Kit - includes E-mount, MOLLE retainer and paracord	080926-14137-7	14137	
Paracord	080926-14138-4	14138	
Sidewinder Rescue Accessory Kit - includes MOLLE retainer and paracord	080926-14319-1	14139	
Lithium batteries - 2 Pack	080926-85175-7	85175	
Lithium batteries - 12 Pack	080926-85177-1	85177	
Lithium batteries - 400 Pack	080926-85179-5	85179	
Lithium batteries - 6 Pack	080926-85180-1	85180	









