

Cat5e 350 MHz Snagless Molded Slim UTP Patch Cable (RJ45 M/M), Blue, 3 ft.

MODEL NUMBER: **N001-S03-BL**



Description

The N001-S03-BL Cat5e 350 MHz Snagless Molded Slim UTP Patch Cable is perfect for connecting network components like printers, computers, copiers, routers, servers, modems and switches in high-density data centers. Designed for fast transmission and excellent signal quality, this three-foot blue cable ensures peak performance throughout your local area network (LAN).

Manufactured from 28 AWG copper wire, the four-pair stranded UTP N001-S03-BL delivers speeds up to 350 MHz/1 Gbps. Protected by a PVC jacket, this cable is more than 25% smaller in diameter than standard Cat5e cable, which increases airflow in tight spaces and makes it easier to install around corners and through cable management panels.

RJ45 male connectors guarantee an accurate signal transfer. The snagless design protects the locking tabs against being damaged or broken off during installation. Integral strain relief ensures the cable and connectors last a long time.

Features

Perfect Solution for Your Networking Needs

- Ideal for connecting components like printers, computers, copiers, routers, servers, modems and switches in high-density data centers
- Designed for fast transmission and excellent signal quality
- Ensures peak performance throughout your LAN
- Delivers speeds up to 350 MHz/1 Gbps

Special Slim Design

- More than 25% smaller in diameter than standard Cat5e cable

Highlights

- Over 25% slimmer than standard Cat5e cables
- Rated for 350 MHz/1 Gbps communications
- Snagless RJ45 male connectors
- Easy to route through cable management panels
- High-quality 28 AWG copper wire

Package Includes

- N001-S03-BL Cat5e 350 MHz Snagless Molded Slim UTP Patch Cable (RJ45 M/M), 3 ft.



- Increases airflow in tight spaces
- Extra flexible for installing around corners and through cable management panels

Premium Construction for Superior Performance

- Made from 28 AWG copper wire
- PVC 4-pair stranded UTP
- RJ45 male connectors
- Integral strain relief for long life

Snagless Connectors

- Molded snagless boots prevent locking tabs from damage

Specifications

MODEL TEXT	
Key Benefit	Connects network components like printers, computers, copiers, routers, servers, modems and switches. Ideal for high-density data centers. Slim design increases airflow in tight spaces.
INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.9
PHYSICAL	
Color	Blue
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
CERTIFICATIONS	
Certifications	RoHS-Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>