

## Mini DisplayPort 1.2 to DVI Active Adapter Cable, Mini DP to DVI (M/M), 1920 x 1080/1080p, 3 ft.

MODEL NUMBER: **P586-003-DVI-V2**



### Highlights

- Active adapter cable for use with any Mini Displayport (or Thunderbolt) port
- Supports HD video resolution up to 1920 x 1080 (1080p)
- No separate adapter required
- Gold-plated connectors and contacts

### Package Includes

- P586-003-DVI-V2 Mini DisplayPort 1.2 to DVI Active Adapter Cable, 3 ft.

### Description

The P586-003-DVI-V2 Mini DisplayPort 1.2 to DVI Active Adapter Cable connects a Mini DisplayPort (or Thunderbolt) computer to the DVI port on a monitor, projector or television. With a Mini DisplayPort male connector on one end and a DVI-D male connector on the other, this cable requires no separate adapter. It lets you use your existing DVI display instead of buying a new Mini DisplayPort monitor.

Ideal for displaying video on a large monitor or digital sign, this cable supports high-definition video resolutions up to 1920 x 1080 (1080p). It converts both Single-Mode and Dual-Mode (DP++) Mini DisplayPort output, and is perfect for use with graphics cards, such as AMD Eyefinity, that don't output DP++ signals.

First-class foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI interference. Gold-plated connectors and contacts ensure excellent conductivity. Integral strain relief ensures the cable and molded connectors last a long time.

### Features

Send High-Quality Mini DisplayPort v1.2 Video Signals to a DVI Display

- Connects Mini DisplayPort (or Thunderbolt) computer to DVI-enabled monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- Mini DisplayPort and DVI-D male connectors
- No separate adapter required

Vibrant, Superior Video Quality

- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Converts Single-Mode and Dual-Mode (DP++) Mini DisplayPort output



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

- Perfect for use with graphics cards, such as AMD Eyefinity, that don't output DP++ signals

#### Superior Materials for Superior Performance

- Double shielding with foil and braid for maximum EMI/RFI protection
- Gold-plated connectors and contacts for excellent conductivity
- Integral strain relief for long life

## Specifications

MODEL TEXT	
Key Benefit	Converts a Mini DisplayPort v1.2 video signal for display on a DVI monitor, projector or television.
INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.9
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D DUAL-LINK (MALE) (WIRED TO DVI-D SINGLE-LINK)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>