

MODEL	TYPE - GENDER	LGT/FT	1-9	10-24	25-99
-------	---------------	--------	-----	-------	-------

**RG59A/U - 75 Ohm Premium Audio/Video Cables Have Popular BNC, RCA & F Plugs**

Today's mixed use of data, video and sound brings about a varied need for high quality coaxial cables with combined use of BNC, F and RCA connectors. This series features a stranded center conductor rather than the conventional solid found in traditional RG59 cables. This provides added flexibility that resists severe twisting, bending and other stresses which occur with frequent handling. Other features include: gold flash on all connector surfaces, and a new type of molding (style) on the connector which serves as a very efficient strain relief. The F type has captivated gold plated center pin (not the typical center wire). Although stocked only in five lengths, we solicit quantity quote requests for your specific needs.

<p><b>RG59A/U</b> 0.240 in. Nominal <b>75 Ohm Impedance</b></p>	<ul style="list-style-type: none"> <li>Center Conductor: 23 (7x32) AWG bare compacted copper</li> <li>Shielding: Bare copper braid (95% coverage)</li> <li>Insulation: Foam polyethylene</li> <li>Jacket: Black PVC</li> <li>Operating Temperature: -40°C - +80°C</li> </ul>	NOMINAL ATTENUATION		
		MHz	db/100ft	db/100m
		50	2.8	9.2
		100	4.0	13.1
		200	5.9	19.4
		400	8.5	27.9
		1000	13.8	45.3

**RG59A/U - 75 Ohm Coaxial Cable with Two In-Line RCA Molded Plugs**

CC59A-RR-1	RCA Male / RCA Male	1.0	3.05	2.81	2.56
CC59A-RR-3	RCA Male / RCA Male	3.0	3.75	3.45	3.15
CC59A-RR-6	RCA Male / RCA Male	6.0	4.80	4.42	4.03
CC59A-RR-9	RCA Male / RCA Male	9.0	5.85	5.38	4.91
CC59A-RR-12	RCA Male / RCA Male	12.0	6.90	6.35	5.80

**RG59A/U - 75 Ohm Coaxial Cable with One Molded RCA and One Molded BNC Plug**

CC59A-RB-1	RCA Male / BNC Male	1.0	3.70	3.40	3.11
CC59A-RB-3	RCA Male / BNC Male	3.0	4.40	4.05	3.70
CC59A-RB-6	RCA Male / BNC Male	6.0	5.45	5.01	4.58
CC59A-RB-9	RCA Male / BNC Male	9.0	6.50	5.98	5.46
CC59A-RB-12	RCA Male / BNC Male	12.0	7.55	6.95	6.34

**RG59A/U - 75 Ohm Coaxial Cable with One Molded RCA and One Molded F Plug**

CC59A-RF-1	RCA Male / F Male	1.0	3.15	2.90	2.65
CC59A-RF-3	RCA Male / F Male	3.0	3.85	3.54	3.23
CC59A-RF-6	RCA Male / F Male	6.0	4.90	4.51	4.12
CC59A-RF-9	RCA Male / F Male	9.0	5.95	5.47	5.00
CC59A-RF-12	RCA Male / F Male	12.0	7.00	6.44	5.88

**RG59A/U - 75 Ohm Coaxial Cable with One Molded BNC and One Molded F Plug**

CC59A-BF-1	BNC Male / F Male	1.0	3.80	3.50	3.19
CC59A-BF-3	BNC Male / F Male	3.0	4.50	4.14	3.78
CC59A-BF-6	BNC Male / F Male	6.0	5.55	5.11	4.66
CC59A-BF-9	BNC Male / F Male	9.0	6.60	6.07	5.54
CC59A-BF-12	BNC Male / F Male	12.0	7.65	7.04	6.43

**RG59A/U - 75 Ohm Coaxial Cable with Two Molded F Plugs**

CCF59-1	RG59 Video Cable, Male / Male	1.0	3.25	2.99	2.73
CCF59-3	RG59 Video Cable, Male / Male	3.0	3.95	3.63	3.32
CCF59-6	RG59 Video Cable, Male / Male	6.0	5.00	4.60	4.20
CCF59-9	RG59 Video Cable, Male / Male	9.0	6.05	5.57	5.08
CCF59-12	RG59 Video Cable, Male / Male	12.0	7.10	6.53	5.96
CCF59-25	RG59 Video Cable, Male / Male	25.0	11.65	10.72	9.79
CCF59-50	RG59 Video Cable, Male / Male	50.0	20.40	18.77	17.14
CCF59-100	RG59 Video Cable, Male / Male	100.0	37.90	34.87	31.84

**RG6/U - 75 Ohm Coaxial Cable with Two Molded F Plugs**

CCF6-1	RG6 Video Cable, Male / Male	1.0	5.34	4.91	4.49
CCF6-3	RG6 Video Cable, Male / Male	3.0	6.12	5.63	5.14
CCF6-6	RG6 Video Cable, Male / Male	6.0	7.29	6.71	6.12
CCF6-9	RG6 Video Cable, Male / Male	9.0	8.46	7.78	7.11
CCF6-12	RG6 Video Cable, Male / Male	12.0	9.63	8.86	8.09
CCF6-25	RG6 Video Cable, Male / Male	25.0	14.70	13.52	12.35
CCF6-50	RG6 Video Cable, Male / Male	50.0	24.45	22.49	20.54
CCF6-100	RG6 Video Cable, Male / Male	100.0	43.95	40.43	36.92

**Variety of Interseries Adaptors - Mate F with Other Types of Connector Interfaces**

BA120	F Male to BNC Female	1.95	1.79	1.64
BA123	F Female to F Male, Right Angle	1.95	1.79	1.64
BA124	F Male Push-on to F Female	1.25	1.15	1.05
BA125	F Female to BNC Male	1.95	1.79	1.64
BA132	F Female T Adaptor	3.45	3.17	2.90
BA220	F Female to BNC Female	2.35	2.16	1.97
BA330A	F Bulkhead Feed-Thru (.5 D-Hole) w/Insul. Washer	1.95	1.79	1.64
BA887	F Female to RCA Female	1.75	1.61	1.47
BA907	F Female to RCA Male	1.75	1.61	1.47

NOTE: Please ask for discounted prices in quantities of 100 and more

Order Toll Free: 800-343-1455

Web: www.L-com.com

**L-com**

24 Hour Fax Service: 978-689-9484

E-mail: sales@L-com.com

MON. - THURS. 8am-6pm, FRI. 8am-5pm EST

N. ANDOVER, MA 01845

PRICES AND SPECIFICATIONS SUBJECT TO CHANGE.

