



ENGLISH

Datasheet

RS Pro LED 3 AAA 400 LM High Power Torch

RS Stock No: 901-4979



Sizes:

Torch Overall Length (mm):	144
Diameter (Ø mm):	Head - Ø 40, Barrel – Ø 29
Batteries Inserted:	3 X AAA
Batteries Supply:	Included
Weight (gm), Torch Only:	144



ENGLISH

Features

Depressing Barrel Switch

Switching Modes – High ON/Low ON/OFF

Functioned by 3 X AAA Batteries

Carrying Holster Included

Built-in Multi Option Battery Holder in Use – 3 X AAA, 2 X AAA or 1 X AAA

Lumen Output (ANSI FL1 STANDARD):

3 X AAA – 400 LM at High, 150 LM at Low

2 X AAA – 200 LM at High, 70 LM at Low

1 X AAA – 100 LM at High, 30 LM at Low

Battery Run Time (100% to 10%, ANSI FL1 STANDARD):

3 X AAA – 5 Hrs at High, 15 Hrs at Low

2 X AAA – 3.5 Hrs at High, 10.5 Hrs at Low

1 X AAA – 2.5 Hrs at High, 7.5 Hrs at Low

Battery Power Indicator: On Grip, the indicator turned from GREEN to RED when power is less than 20%

Water Resistant: IPX6

Drop Impact Test: 1 Meter

Taiwan and USA Patented

Materials/Parts

Case: 6463 Aluminium Alloy

Lens: PC

LED: CREE X-PL V4

Package: Folded PVC Blister with RS Card Inserted