

HD Video Transceiver with Pigtail (Balun)

TVIUTPPT



Features

- Send HD-TVI signal up to 656' (200M) over UTP cable.
- BNC male to screw terminal with 4" (10cm) mini coax cable for easy connection.
- Compact size allows mounting of multiple units behind multiplexers, Quads, DVRs, etc.
- Passive, No power required.
- Ideal for retrofits using existing UTP cable.
- Built in ESD, EFT (impulse noise), lightning (surge) and transient protection.
- Used in pairs (Sold individually).
- Sold individually but used in pairs. Could be used in conjunction with another TVIUTPPT, or with the non-pigtail model **TVIUTP**

Specifications

Video Input / Output Terminals BNC Male 1Vp-p, 75 Ohms
 Video On Put / Output Terminals Terminal Block
 Bandwidth..... 50Hz - 60MHz (-3dB)
 Transmission Distance HD-TVI: 656' (200M)
 ESD Protection 30 KV(air) | 15 KV (contact) ; complaint IEC 61000-4-2
 EFT Protection..... 40A(5/50ns) ; IEC 61000-4-4 compliant
 Lighting Protection..... 2A (8/20µs) ; IEC 61000-4-5 compliant
 Surge Protection Startup Time < 1 nS
 Operating Temperature..... 32° F - 131° F,
 Storage Temperature/Humidity..... -4° F - 185° F / up to 95%
 Dimensions..... 0.6" (W) x 2" (H) x 0.6" (L)
 Weight 0.64 oz.

Also Available



TVIUTP
HD Video
Transceiver

Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 9/16/15