

#### APPLICATION:

Generally for Ammeter use only FREQUENCY: 50-400 Hz. INSULATION LEVEL: 600 Volts. 10 kV BIL. full wave WINDOW: 1:00", 1.05", 1.13"

#### APPROXIMATE WEIGHT: 0.5 lbs.

## CONNECTIONS:


-Flexible Leads are UL 1015 105°C, CSA approved #16 AWG, 24" long -Non-standard length to be specified -Terminals are brass studs No. 8-32 UNC

with one flat washer, lockwasher, and regular nut

-SHT and SFT case styles also available as SHL or SFL with Leads

-Mounting bracket for Model 2SHT part 59-0217

### **Current Transformer**



2RI

2DRI

Model	2SHT	2SFT	2RL	2DRL
Window Size	1.13	1.13	1.05	1.00
Width	2.40	2.40	2.46	2.42
Height	2.71	2.68	2.46	2.42
Depth	0.95	2.00	1.05	1.75

#### MODEL 2 Window Diameter 1.00", 1.05", 1.13" Approximate weight: 0.5 lbs.

· · · · · · · · · · · · · · · · · · ·									
CATALOG NUMBER	CURRENT RATIO	MODELS 2SFT, 2SHT, 2RL		MODEL 2DRL					
		ACCURACY AT 60 HZ	BURDEN VA AT 60 HZ	ACCURACY AT 60 HZ	BURDEN VA AT 60 HZ				
2**-250	25.5	-	-	<u>+</u> 5%	1				
2**-500	50:5	<u>+</u> 4%	1	<u>+</u> 2%	1.5				
2**-600	60:5	<u>+</u> 3%	2	<u>+</u> 2%	2				
2**-750	75:5	<u>+</u> 3%	2	<u>+</u> 2%	3				
2**-800	80:5	<u>+</u> 2%	2	<u>+</u> 2%	4				
2**-101	100:5	<u>+</u> 1%	2	<u>+</u> 1%	5				
2**-121	120:5	<u>+</u> 1%	2.5	<u>+</u> 1%	5				
2**-1250	125:5	<u>+</u> 1%	2.5	<u>+</u> 1%	5				
2**-151	150:5	<u>+</u> 1%	4	<u>+</u> 1%	8				
2**-181	180:5	<u>+</u> 1%	4	<u>+</u> 1%	10				
2**-201	200:5	<u>+</u> 1%	4	<u>+</u> 1%	10				
2**-251	250:5	<u>+</u> 1%	6	<u>+</u> 1%	12.5				
2**301	300:5	<u>+</u> 1%	8	<u>+</u> 1%	15				
2**-331	330:5	<u>+</u> 1.2%	10	<u>+</u> 1%	17.5				

NOTE: When ordering, Prefix Cat. No. With model designation required, i.e. 2SFT-301, 2RL-301, or 2SHT-301 or 2DRL-301

# Model 2

### **CERTIFICATIONS**:







237637


Products are manufactured in a plant whose quality management system is certified / registered as being in conformity with ISO 9001














2DRL

