LED Lights

LED Rotating Swivel Lights

- Ideal for Tiny Houses, Mobile Homes, Trailers, RVs and Boats
- **Available in Clear or Frosted Lenses**
- Flexible, 180° Rotation for Easy Angle Adjustment
- Compact Size with Fashionable Design and Easy Assembly
- 4 LEDs per Light
- 2 Inch Power Lead Wires

Specifications

Rating: 12 / 24VDC, 25mA / 10mA (69–LL–02) 12 / 24VDC, 2W at 13.6V (69–LL–03, 69–LL–04)

LED Type: SMD, 0.3W **(69–LL–02)**

SMD, 0.5W (69–LL–03, 69–LL–04) Insulation Resistance: $100M\Omega$, 500VAC Min Dielectric Strength: 100VAC, 1 Minute Operating Temperature: -20° to +60°C


Base Color: Satin / White



Ordering Information

NTE Type No.	LED Color / CCT	Lens Type	Switch	Power Consumption	Output Illumination (Lux)
69-LL-02	Cold White (17671K)	Clear	Yes	1.2W	12VDC, 30.5 ±20%
69-LL-03	White (4000K)	Frosted	No	2.0W	13.6VDC, 27 ±20%
69-LL-04	White (4000K)	Frosted	Yes	2.0W	13.6VDC, 27 ±20%

Dimensions



	L	Н	М
69-LL-02	6.850 (174.0)	1.181 (30.0)	5.590 (142.0)
69-LL-03	6.850 (174.0)	1.181 (30.0)	5.590 (142.0)
69-LL-04	7.362 (187.0)	1.299 (33.0)	6.102 (155.0)

Mounting Instructions:

- 1. Remove end covers by sliding away from the light.
- 2. Drill .079" (2.0mm) pilot holes for screws or rivets.
- 3. Install screws or rivets to secure light.
- 4. Replace end covers.