

## Thermomagnetic device circuit breaker - TMC 81C 01A - 2907558

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Thermomagnetic device circuit breaker, Width: 17.6 mm, Mounting type: DIN rail, Color: gray



### Key Commercial Data

Packing unit	1 STK
Weight per Piece (excluding packing)	150.0 g
Country of origin	China

### Technical data

#### General

Mounting type	DIN rail
Color	gray

#### Electrical data

Operating voltage	240 V AC
	277 V AC
	60 V DC
Rated current $I_N$	1 A
Rated short-circuit switching capacity $I_{cn}$	10 kA (IC)

#### Dimensions

Height	116 mm
Width	17.6 mm
Depth	65.7 mm

#### Ambient conditions

# Thermomagnetic device circuit breaker - TMC 81C 01A - 2907558

## Technical data

### Ambient conditions


Ambient temperature (operation)	-35 °C ... 70 °C
---------------------------------	------------------

### Standards and Regulations


Standards/specifications	UL 489 IEC 60947-2
--------------------------	--------------------

## Drawings

Diagram



Dimensional drawing



## Classifications

### eCl@ss

eCl@ss 8.0	27130806
eCl@ss 9.0	27130806

### ETIM

ETIM 5.0	EC000942
----------	----------