

Product type designation

IWLAN RCoax connector N-Connect Female N-Connector  
IWLAN RCOAX N-CONNECT FEMALE N-CONNECTOR 2.4 AND 5  
GHZ CAN BE PRE-ASSEMBLED IN THE FIELD COAXIAL CABLE  
TAP FOR CONNECTING THE RCOAX CABLE TO FURTHER  
COMPONENTS



Electrical data	
Number of electrical connections	1
Type of electrical connection	N-Connect female
Transmission frequency	0 ... 6 GHz
Impedance	50 Ω
Permitted ambient conditions	
Ambient temperature	
• during operation	-40 ... +85 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
Protection class IP	IP67
Design, dimensions and weight	
Diameter	27 mm
Length	65 mm
Net weight	159 g
Standards, specifications, approvals	
Certificate of suitability	

- RoHS conformity

Yes

## Further Information / Internet Links

### Internet-Link

- to website: Selector SIMATIC NET SELECTION TOOL
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<http://www.siemens.com/snst>

<http://www.siemens.com/simatic-net>

<https://mall.industry.siemens.com>

<http://www.siemens.com/industry/infocenter>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

**last modified:**

07/20/2016