

Product type designation

MM992-4SFP

SCALANCE X ACCESSORIES; MEDIA MODULE MM992-4SFP; 4 X 100/1000MBIT/S FOR SFP PLUG TRANSCEIVER



Interfaces

Number of electrical/optical connections / for network components or terminal equipment / maximum	4
Number of electrical connections	
<ul style="list-style-type: none"> • for SFP / plug-in 	4

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> • during operation • during storage • during transport 	<p>0 ... 60 °C</p> <p>-40 ... +85 °C</p> <p>-40 ... +85 °C</p>
Relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
Protection class IP	IP20

Design, dimensions and weight

Design	Media module
Width	120.3 mm
Height	22.3 mm
Depth	275.5 mm

Net weight	0.3 kg
Mounting type	latched
<ul style="list-style-type: none"> • Installation in media module slot 	Yes

Standards, specifications, approvals

Standard	
<ul style="list-style-type: none"> • for safety / from CSA and UL • for emitted interference • for interference immunity 	UL 60950-1, CSA C22.2 No. 60950-3 EN 61000-6-4 (Class A) EN 61000-6-2
Certificate of suitability	EN 61000-6-2:2005, EN 61000-6-4:2007
<ul style="list-style-type: none"> • CE marking • C-Tick • KC approval • E1 approval 	Yes Yes Yes No

Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> • to website: Selector SIMATIC NET SELECTION TOOL • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAx Download Manager • to website: Industry Online Support 	http://www.siemens.com/snst http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

last modified: 07/08/2016