



FREE catalogue!


+91 (0) 80 4545 3676

[Home](#) [Products](#) [About Us](#) [Locations](#) [Contact Us](#) [Shopping Cart](#)

Cable Ties and Accessories

- Standard Cable Ties
- Coloured Cable Ties
- Cable Tie Kits
- Heavy-Duty Cable Ties
- UV-Resistant Cable Ties
- Flame Retardant Cable Ties
- High Temperature Cable Ties
- Heat Stabilized Cable Ties
- Cable Tie Guns
- Releasable Ties
- Release Tab Wrap-It Tie
- Low Profile Cable Ties
- Double-Loop Cable Ties
- Double-Locking Cable Ties
- Stainless Steel Cable Tie Installation Tool
- Stainless Steel Cable Ties
- Stainless Steel Ladder Ties
- Metal Detectable Cable Ties
- Coated Steel Ladder Ties
- Coated Stainless Steel Cable Ties
- Cable Ties with Stainless Steel Tooth
- Beaded Tie
- Locking Beaded Tie
- Beaded Wire Tie
- Beaded Hanking Tie
- Hanking Tie
- Push Mount Ties - SR1769
- Push Mount Ties - WIT-50RLA
- Push Mount Ties - WIT-RA/WIT-SA
- Push Mount Ties - WIT-18RA
- Push Mount Ties - WIT-30RRA
- Releasable Push Mount Ties - WIT-30RAR/WIT-30LAR
- Releasable Push Mount Ties - WIT-40LAR
- Screw Mount Ties
- Adhesive/Screw Mount Tie
- Rivet Mount Cable Tie
- Blind Hole Mount Cable Ties
- Cupped Cable Ties
- Tie On Push Mount Cable Ties

Push Mount Cable Tie Holder - FTH-6



Part No.	Colour	Material	Hole Ø (mm)	Panel Thickness (mm)	Max Cable Tie Width Accepted (mm)				
FTH-6-01-M	Natural	UL94 V2 Nylon 6/6, RMS-01	6.35 ± 0.08	1.19 - 2.77	6.6	Price	3D	Sample	Buy
FTH-6-01BK-M	Black	UL94 V2 Nylon 6/6, RMS-01	6.35 ± 0.08	1.19 - 2.77	6.6	Price	3D	Sample	Buy
FTH-6-19-M	Natural	UL94 V0 Nylon 6/6, RMS-19	6.35 ± 0.08	1.19 - 2.77	6.6	Price	3D	Sample	Buy