



[All Series](#) > [Series 45](#) > Part No. 45-1828.3C90.001.408

**Part No. 45-1828.3C90.001.408, Selector switch**

[Request Information](#)

[Printable Page](#)

[Download PDF](#)


[Email This Page](#)



[3D CAD DRAWING](#)




[3D](#)



[Front View](#)


45-1828.3C90.001.408



[2D Right Side View](#)



[2D Top View](#)



[2D Sales Drawing](#)

[Specifications](#) | [Bill of Materials](#)

**Specifications**

Actuator	<a href="#">Selector switch</a>
Lens Colour	White

Function	2 Pos., maint. (L-R)
Housing Material	Metal/Plastic
Shape of Handle or Frontring	Short handle
Lock System	None
Key	None
Key Type	None
Switching Angle	90 Grad (V-Pos)
Contacts	1NO, 1NC
Terminal	Spring-loaded terminal
Voltage Illumination	None
Mounting Type	Front mounting
Mounting Style	Holder
Environmental Rating	IP66, IP67, IP69K
Industry Standards/Certifications	UL, CSA, VDE, CCC, CE, RoHS
Switching Function	On-Off
Illumination	None
Contact Material	Silver
Termination Style	Spring type
Mechanical Life	1'000'000 switching cycles
AC Voltage	500 V
DC Voltage	500 V
Switching Current	10 A

**Bill of Materials**

Actuator	45-2828.3C90.001

Holder	45-2300.1000.000
Switch Element 1	45-311.1Z40
Switch Element 2	45-312.1Z40