

WXR3 Rework Station NEW

Weller[®]
PRODUCT INFORMATION

Multifunctional WXR3 can be used simultaneously with a soldering iron, desoldering iron and hot air pencil.



- Up to three 200w high performance tools can be operated simultaneously for up to 600 watts of total power on the 3-channel, WXR3 rework system
- Used for soldering and desoldering of both large and small SMT components
- 2 internal pumps provide the sources for hot air, desoldering vacuum and a vacuum pick up tool for a completely self-contained rework system
- LCD display simultaneously monitors all parameters, connected tools and peripheral devices. Adjust parameter setting and other functions through menu.
- Compatible with all WX tools, accessories, and peripherals

TOOL COMPARISON BY SET

Catalog & order no.	WXR3	WXR3001 SET*	WXR3002 SET*	WXR3003 SET*
Hot air pencil	N / A	WXHAP200 (200w / 24v)	WXHAP200 (200w / 24 v)	WXHAP200 (200w / 24v)
Desoldering iron	N / A	WXDP120 (120w / 24v)	WXDP120 (120w / 24 v)	WXDV120 (120w / 24v)
Soldering iron	N / A	WXP65 (65w / 24v)	WXP120 (120w / 24v)	WXP65 (65w / 24v)

***All sets include:** the WXR Rework Station, hot air pencil with nozzles, desoldering iron and soldering iron with tips, WVP vacuum pickup pen with cups, desoldering triplet, and WDH30, WDH70, WDH10 safety rests.





Soldering irons



WXP65 (65w / 24v)
Order no. T0052921199



WXP120 (120w / 24v)
Order no. T0052920199



Desoldering irons



WXDP120 (120w / 24v)
Order no. T0051320199



WXDV120 (120w / 24v)
Order no. T0051320499



Hot air pencil



WXHAP200 (200w / 24v)
Order no. T0052711999



All sets include:

- WXR rework unit
- Hot air pencil / nozzles
- Desoldering iron / tips
- Soldering iron / tips
- WVP vacuum pickup pen / vacuum cups
- Desoldering tiplet
- 3 safety rests



WXR3001 and WXR 3002 sets come with WDH30, WDH70, WDH10 safety rests.
WXR3003 set comes with WDH40, for the WXDV120 desoldering iron.

SPECIFICATIONS

Power consumption	420w (600w)
Temperature range	Sold./Desold. 100°C – 450°C (200°F – 850°F) Hot air pencil 100°C – 550°C (200°F – 999°F)
Temperature accuracy	Soldering ± 17°F (± 9°C) Hot air ± 54°F (± 30°C) Desoldering ± 17°F (± 9°C)
Temperature stability	± 4°F (± 2°C)
Mains supply	120 VAC / 60Hz
USB interface and RS 232 interface	
Pump	Intermittant mode: max. hot air 15 l/min Max. vacuum 0.5 bar, max. delivery rate 1.7 l/min
Supplied tips	WXP65 XTNA WXP120 XTB WXDP120 XDS3, XDS5 WXDV120 XDS3, XDS5 WXHAP200 R04, R06
ESD safe	yes

ORDER INFORMATION

Package length	10.75 in
Package width	9.25 in
Package height	4.02 in
Package gross weight	6.7 kg
UPC	WXR3 037103288653 WXR3001 037103288684 WXR3002 037103288677 WXR3003 037103288660
Country of origin	Germany
Foreign trade code	(Kits) 8515110000 (WXR3) 8515190000

