

# Conductor marker carrier - PATG 3/10 - 1013821

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marker carrier, transparent, unlabeled, mounting type: slide on, cable diameter range: 4 - 7 mm, lettering field size: 10 x 4 mm

## Why buy this product

- The corresponding UC-WMT ..., US-WMT ..., and EMT ... insert labels are used for marking
- The PATG ... collar is a captive marker carrier
- These conductor marking systems consist of marker carriers and insert labels
- Can be used to mark conductors with a diameter of 0.6 ... 50 mm

## Key Commercial Data

Packing unit	500 STK
Minimum order quantity	500 STK
GTIN	
GTIN	4017918014018

## Technical data

### Dimensions

Length (b)	10 mm
Width (a)	7.5 mm
Cable diameter	4 mm ... 7 mm

### Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
---------------------------------	------------------

### General

Color	transparent
Type	Profile
Components	Silicone-free
Flammability rating according to UL 94	V0

## Conductor marker carrier - PATG 3/10 - 1013821

### Technical data

#### General

Material	PVC
RoHS compliant	Yes
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Marking mounting type	slide on
Min. cross section	4 mm <sup>2</sup>
Max. cross section	7 mm <sup>2</sup>

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

---

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>